



Omron Automation & Safety

A22NZ-MPM-NBA

Karolo ea Karolo:

Moetsi / Mochini:

Tlhaloso ea Sehlahisoa

Datasheets:

Boemo ba RoHs

Sekepe se Tsoang ho

Tsela ea Shipment

A22NZ-MPM-NBA

Omron Automation & Safety

CONFIG SW BODY PUSHBUT NON-ILLUM

 A22NZ-MPM-NBA.pdf

 Tataiso ea mahala / RoHS e lumellanang

Hong Kong

DHL/Fedex/TNT/UPS/EMS




Setšoantšo e kanna ea ba moemeli. Bona litlhaloso bakeng sa lintlha tsa sehlahisoa.

KOPO EA HO

QOTSA










Litlhaloso tsa A22NZ-MPM-NBA

KAROLO EA KAROLO	A22NZ-MPM-NBA
MOETSI	Omron Automation & Safety
TLHALOSO	CONFIG SW BODY PUSHBUT NON-ILLUM
TEMO EA MAHALA EA BOEMO BO PHAHAMENG / BOEMO BA ROHS	Tataiso ea mahala / RoHS e lumellanang
LEQEPHE LA LINTLHA	 A22NZ-MPM-NBA.pdf
THAPA	Momentary
SEHLOOHO	A22NN
E HLOKA	Contact Block(s)
PANEL DIMENSION DIMENSIONS	22.3mm (Round)
MABITSO A MANG	A22NZMPMNBA
MOKHOA OA HO UTLOISISA BOHLOKO (MSL)	1 (Unlimited)
NAKO EA MOETA-PELE E TLOAELEHILENG	2 Weeks
TEMO EA MAHALA EA BOEMO BO PHAHAMENG / BOEMO BA ROHS	Lead free / RoHS Compliant
HO KHANYA	Non-Illuminated
TLHALOSO E QAQILENG	Configurable Switch Body Pushbutton, Round Non-Illuminated
MOFUTA OA MOFUTHU	Pushbutton, Round
(KHETHA PELE, EBE O SEBELISA FILTER) SEHLOPHA SE LUMELLANANG	Omron, A22NN

Metsu e amanang

Omron Automation & Safety A22NZ-MPM-NBA	Morekisi oa A22NZ-MPM-NBA	Mofani oa A22NZ-MPM-NBA
Theko ea A22NZ-MPM-NBA	A22NZ-MPM-NBA Litšoantšo	Setšoantšo sa A22NZ-MPM-NBA
Datasheet ea PDF ea A22NZ-MPM-NBA	A22NZ-MPM-NBA Download Datasheet	Datasheet ea A22NZ-MPM-NBA
A22NZ-MPM-NBA Stock	Reka A22NZ-MPM-NBA	Reka Omron Automation & Safety A22NZ-MPM-NBA
Omron Automation & Safety A22NZ-MPM-NBA	Mofani oa Omron Automation & Safety	Morekisi oa Omron Automation & Safety
Omron Automation & Safety A22NZ-MPM-NBA	Omron Automation and Safety A22NZ-MPM-NBA	

Lihlahisoa tse amanang

 <p>A22NZ-MPA-UWA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPA-UGA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
 <p>A22NZ-MPM-TAA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPM-NGA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
 <p>A22NZ-MPM-NYA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPM-NAA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
 <p>A22NZ-MPM-NRA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPM-NWA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: 20 pcs</p> <p>RFQ</p>
 <p>A22NZ-MPA-URA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPM-TGA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: 20 pcs</p> <p>RFQ</p>
 <p>A22NZ-MPA-UOA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	 <p>A22NZ-MPA-UYA Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>