



Omron Automation & Safety

A22NZ-BPA-NRA

Karolo ea Karolo:

Moetsi / Mochini:

Tlhaloso ea Sehlahisoa

Datasheets:

Boemo ba RoHS

Sekepe se Tsoang ho

Tsela ea Shipment

A22NZ-BPA-NRA

Omron Automation & Safety

CONFIG SW BODY PUSHBUT NON-ILLUM

A22NZ-BPA-NRA.pdf

Tataiso ea mahala / RoHS e lumellanang

Hong Kong

DHL/Fedex/TNT/UPS/EMS



KOPO EA HO

QOTSA

Setšoantšo e kanna ea ba moemeli. Bona litlhaloso bakeng sa lintlha tsa sehlahisoa.

Litlhaloso tsa A22NZ-BPA-NRA

KAROLO EA KAROLO	A22NZ-BPA-NRA
MOETSI	Omron Automation & Safety
TLHALOSO	CONFIG SW BODY PUSHBUT NON-ILLUM
TEMO EA MAHALA EA BOEMO BO PHAHAMENG / BOEMO BA ROHS	Tataiso ea mahala / RoHS e lumellanang
LEQEPHE LA LINTLHA	A22NZ-BPA-NRA.pdf
THAPA	Maintained
SEHLOOHO	A22NN
E HLOKA	Contact Block(s)
PANEL DIMENSION DIMENSIONS	22.3mm (Round)
MABITSO A MANG	A22NZBPANRA
MOKHOA OA HO UTLOISISA BOHLOKO (MSL)	1 (Unlimited)
NAKO EA MOETA-PELE E TLOAELEHILENG	2 Weeks
TEMO EA MAHALA EA BOEMO BO PHAHAMENG / BOEMO BA ROHS	Lead free / RoHS Compliant
HO KHANYA	Non-Illuminated
TLHALOSO E QAQILENG	Configurable Switch Body Pushbutton, Round Non-Illuminated
MOFUTA OA MOFUTHU	Pushbutton, Round
(KHETHA PELE, EBE O SEBELISA FILTER) SEHLOPHA SE LUMELLANANG	Omron, A22NN

Metsu e amanang

Omron Automation & Safety A22NZ-BPA-NRA	Morekisi oa A22NZ-BPA-NRA	Mofani oa A22NZ-BPA-NRA
Theko ea A22NZ-BPA-NRA	A22NZ-BPA-NRA Litšoantšo	Setšoantšo sa A22NZ-BPA-NRA
Datasheet ea PDF ea A22NZ-BPA-NRA	A22NZ-BPA-NRA Download Datasheet	Datasheet ea A22NZ-BPA-NRA
A22NZ-BPA-NRA Stock	Reka A22NZ-BPA-NRA	Reka Omron Automation & Safety A22NZ-BPA-NRA
Omron Automation & Safety A22NZ-BPA-NRA	Mofani oa Omron Automation & Safety	Morekisi oa Omron Automation & Safety
Omron Automation & Safety A22NZ-BPA-NRA	Omron Automation and Safety A22NZ-BPA-NRA	

Lihlahisoa tse amanang

<p>A22NZ-BPA-NYA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	<p>A22NZ-BPA-TAA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
<p>A22NZ-BNM-UWA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	<p>A22NZ-BPA-NBA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
<p>A22NZ-BPA-TGA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	<p>A22NZ-BPA-TOA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
<p>A22NZ-BPA-NGA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	<p>A22NZ-BPA-NWA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: 19 pcs</p> <p>RFQ</p>
<p>A22NZ-BPA-NAA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>	<p>A22NZ-BNM-UYA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>
<p>A22NZ-BNM-URA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUT NON-ILLUM E teng thepeng e teng ka lebenkeleng: 20 pcs</p> <p>RFQ</p>	<p>A22NZ-BPA-TRA</p> <p>Bahlahisi: Omron Automation & Safety Tlhaloso: CONFIG SW BODY PUSHBUTTON ILLUM E teng thepeng e teng ka lebenkeleng: Out stock</p> <p>RFQ</p>

